Memoirs® | K-1418-V

72" x 42" drop-in Effervescence whirlpool bath

Features

- 6 hydromassage jets can be individually adjusted for water flow and direction
- Variable-speed pump for adjusting hydromassage intensity
- Adjustable neckjet pillow with 2 jets provides a stimulating, stress-relieving neck massage
- 10 backjets target the lower back and shoulders to relieve tension and encourage deep breathing
- Chromatherapy lighting allows you to select a preferred color scheme to suit your mood
- Built-in heater
- Remote control
- Lighted keypad control
- Generous length provides a spacious bathing area
- Drilled for grab bars (required); sold separately

Available Colors/Finishes

Color tiles intended for reference only.

0	White
96	Biscuit

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
10-27-2026 17:36 - US-CA

Codes/Standards

ASME A112.19.7/CSA B45.10
CSA B45.5/IAPMO Z124
ASTM E162
ASTM E662
UL 1795
CSA C22.2 No. 218.2
UL Listed

Technical Information

All product dimensions are nominal.

Drain Location:	Center
Drain Hole Diameter:	2-1/4" (57 mm)
Minimum Flat for Door:	3-13/16" (97 mm)
Basin Area, Bottom:	41-3/4" x 27-3/16" (1060 mm x 691 mm)
Basin Area, Top:	60" x 30" (1524 mm x 762 mm)
Water Depth:	16" (406 mm)
Water Capacity:	86 gal (325.5 L)
Minimum Floor Load:	44 lbs/ft²
Weight:	140 lbs (63.5 kg)
Cutout:	Drop-in, 70-1/2" x 40-1/2" (1791 mm x 1029 mm)

Material

- Acrylic

Recommended Products/Accessories

- K-1601 Bath/whirlpool footstop, removable
- K-9696 Whirlpool trim kit with six jets
- [object Object]23726 Drain treatment
- K-23732 Tub & shower cleaner

Required Products/Accessories

- K-9653 Grab bars for whirlpool baths with Spa/Massage package

or

- K-T37392 Rotary-turn bath drain trim
- K-T37391 Rotary-turn bath drain trim

or

- K-78439 45" cable bath drain
- K-37385 Rough-in cable drain, PVC, 45" cable, less horizontal tube

Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Pump:	240 V, 20 A, 50/60 Hz

Electrical Component Ratings

Pump:	240 V, 11 A, 50/60 Hz, 1500 W
Number of Speeds:	Variable

Warranty

See website for detailed warranty information.

KOHLER® Plastic Baths and Shower Bases Lifetime Limited Warranty
KOHLER® Hydrotherapy Components Five-Year Limited Warranty

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
10-27-2026 17:36 - US-CA

THE BOLD LOOK OF KOHLER.



Installation

- Drop-in

Installation Notes

Install this product according to the installation instructions.

Measure your actual product for rough-in details.
The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.
This whirlpool is designed for drop-in installation only. It is not suited for use in a three wall alcove with an overhead shower.
If installing a rim-mount faucet, make sure there is no interference above or below the deck before drilling any holes.

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
10-27-2026 17:36 - US-CA

THE BOLD LOOK OF KOHLER