

Purist® | K-14410-3

Widespread bathroom sink faucet with Cross handles, 1.2 gpm

Features

- Metal construction
- Cross handles
- Reversible quarter-turn washerless ceramic disc valves
- Lower flow aerator options are available
- 1.2 gpm (4.5 lpm) maximum flow rate at 60 psi (4.14 bar)
- Metal touch-activated drain with 1-1/4" tailpiece



Sustainability



Available Colors/Finishes

Color tiles intended for reference only.

- CP Polished Chrome
- SN Vibrant Polished Nickel
- BN Vibrant Brushed Nickel
- BV Vibrant Brushed Bronze
- BL Matte Black
- 2MB Vibrant Brushed Moderne Brass
- TT Vibrant Titanium
- RGD Vibrant Rose Gold
- BGP Vibrant Brushed Graphite



Codes/Standards

ADA compliant when installed to the specific requirements of these regulations.



ADA

ASME A112.18.1/CSA B125.1
NSF/ANSI/CAN 372
NSF/ANSI/CAN 61
DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)
ADA
ICC/ANSI A117.1

Technical Information

All product dimensions are nominal.

Handle

Handle Style/ Type: Cross

Spout

Spout Reach: 5" (127 mm)

Flow Rate

Faucet Flow Rate: 1.2 gpm (4.5 l/min)

Valves

Included Valve: Ceramic disc

Material

- Brass valve bodies
- KOHLER finishes resist corrosion and tarnishing

Recommended Products/Accessories


K-23726 Drain treatment
K-23723 Faucet cleaner
K-14375 24" Double towel bar
K-14436 24" towel bar
K-14443 Robe hook
K-14377 Pivoting toilet paper holder
K-14435 18" towel bar
K-14441 Towel ring
K-14444 Vertical toilet paper holder

Warranty

See website for detailed warranty information.

KOHLER® Faucet Lifetime Limited Warranty





Installation

- For 8" - 16" (203 - 406 mm) centers

Installation Notes

Install this product according to the installation instructions.

ADA compliant for handles only.

ADA compliant when installed to the specific requirements of these regulations.

