

## Purist® | K-14410-4

Widespread bathroom sink faucet with Lever handles, 1.2 gpm

### Features

- Metal construction
- Lever handles
- Reversible quarter-turn washerless ceramic disc valves
- Lower flow aerator options are available
- 1.2 gpm (4.5 lpm) maximum flow rate at 60 psi (4.14 bar)
- Metal touch-activated drain with 1-1/4" tailpiece



### Sustainability



### Available Colors/Finishes

*Color tiles intended for reference only.*

- CP Polished Chrome
- SN Vibrant Polished Nickel
- AF Vibrant French Gold
- BN Vibrant Brushed Nickel
- BV Vibrant Brushed Bronze
- BL Matte Black
- 2MB Vibrant Brushed Moderne Brass
- TT Vibrant Titanium
- BGP Vibrant Brushed Graphite



## Codes/Standards

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.



ADA CSA B651 OBC

ASME A112.18.1/CSA B125.1  
NSF/ANSI/CAN 372  
NSF/ANSI/CAN 61  
DOE - Energy Policy Act 1992  
EPA WaterSense®  
California Energy Commission (CEC)  
ADA  
ICC/ANSI A117.1  
CSA B651  
OBC

## Recommended Products/Accessories

K-23726 Drain treatment  
K-23723 Faucet cleaner  
K-14375 24" Double towel bar  
K-14436 24" towel bar  
K-14443 Robe hook  
K-14377 Pivoting toilet paper holder  
K-14435 18" towel bar  
K-14441 Towel ring  
K-14444 Vertical toilet paper holder

## Warranty

See website for detailed warranty information.

KOHLER® Faucet Lifetime Limited Warranty

## Technical Information

All product dimensions are nominal.

### Handle

Handle Style/ Type: Lever

### Spout

Spout Reach: 5" (127 mm)

### Flow Rate

Faucet Flow Rate: 1.2 gpm (4.5 l/min)


## Valves

Included Valve: Ceramic disc

## Material

- Brass valve bodies
- KOHLER finishes resist corrosion and tarnishing





## Installation

- For 8" - 16" (203 - 406 mm) centers

## Installation Notes

*Install this product according to the installation instructions.*

ADA compliant for handles only.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

