

Features

- One-piece, self-contained ceramic disc valve allows for both volume and temperature control
- High-temperature limit setting for added safety
- Available with straight handle
- Pop-up drain with lift rod and tailpiece
- 4-1/4" (108 mm) swivel spray spout

Material

- Brass

Installation

- Flexible connections for easy installation
- Single-hole mounting

Recommended Products/Accessories

- K-23726 Drain treatment
- K-23723 Faucet cleaner



Codes/Standards









ASME A112.18.1/CSA B125.1
IAPMO Certification


KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	SN	Vibrant® Polished Nickel
	AF	Vibrant® French Gold
	BN	Vibrant® Brushed Nickel
	BV	Vibrant® Brushed Bronze
	BL	Matte Black
	2MB	Vibrant® Brushed Moderne Brass
	TT	Vibrant Titanium



Technical Information

All product dimensions are nominal.

Drain included: Yes

Handshower:

Rated maximum flow: 2.2 gal/min (8.3 l/min)

Notes

Install this product according to the installation instructions.