



Coralais® | K-15275

Two-handle bar sink faucet

Features

- Metal construction
- Quarter-turn washerless ceramic disc valves
- Stationary gooseneck spout
- Gooseneck spout swivels for unobstructed use of the sink
- Sculptured acrylic handles
- Lower flow aerator options are available
- Less drain
- 1.8 gpm (6.8 lpm) maximum flow rate at 60 psi (4.14 bar)



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
7-03-2026 03:38 - US-CA

THE BOLD LOOK
OF **KOHLER**

Codes/Standards

ASME A112.18.1/CSA B125.1
NSF/ANSI/CAN 372
NSF/ANSI/CAN 61
DOE - Energy Policy Act 1992
NSF/ANSI/CAN 61|NSF/ANSI/CAN 372

Technical Information

All product dimensions are nominal.

Handle

Handle Style/Type: Lever

Spout

Spout Reach: 4" (102 mm)

Flow Rate


Faucet Flow Rate: 1.5 gpm (5.7 l/min)

Warranty

See website for detailed warranty information.

KOHLER® One-Year Limited Warranty





Installation

- For 4" (102 mm) centers

Installation Notes

Install this product according to the installation instructions.



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.

7-03-2026 03:38 - US-CA