

Features

- Rectangular basin creates a spacious bathing experience
- Drop-in design creates a seamless bathroom aesthetic
- 59" (1500 mm) x 27-1/2" (700 mm) x 18-1/8" (460 mm)
- Round overflow
- 12-3/4" (324 mm) soaking depth
- Integral lumbar support
- Easy-to-clean, durable high-gloss finish

Material

- Acrylic

Installation

- Drop-in

Required Products/Accessories

K-17295T Pop-up bath drain, 766 mm cable



Codes/Standards

None Applicable


KOHLER® India Vitreous and bathing Product Limited Warranty


See website for detailed warranty
information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	0	White
---	---	-------



Technical Information

All product dimensions are nominal.

Drain location:	Reversible
Basin area, bottom:	53-9/16" x 23-3/4" (1361 mm x 604 mm)
Basin area, top:	39-1/4" x 15-11/16" (996 mm x 399 mm)
Weight:	44.09 lbs (20 kg)
Minimum floor load:	36.6 lbs/ft ² (178.7 kg/m ²)
Water depth:	12-11/16" (322 mm)
Water capacity:	41.33 gal (156.5 L)
Minimum flat for door:	1-7/8" (48 mm)

Notes

Measure your actual product for rough-in details.

Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.