



**Reach™**  
1700 mm x 700 mm drop-in bath  
**K-15848T**

**Features**

- Rectangular basin creates a spacious bathing experience
- Drop-in design creates a seamless bathroom aesthetic
- 67" (1700 mm) x 27-1/2" (700 mm) x 18-1/8" (460 mm)
- Round overflow
- 12-11/16" (322 mm) soaking depth
- Integral lumbar support
- Easy-to-clean, durable high-gloss finish

**Material**

- Acrylic

**Installation**

- Drop-in

**Recommended Products/Accessories**

K-17295T Pop-up bath drain, 766 mm cable



**Codes/Standards**

None Applicable


**KOHLER® India Vitreous and  
bathing Product Limited Warranty**


See website for detailed warranty  
information.

**Available Colors/Finishes**

*Color tiles intended for reference only.*

Color	Code	Description
-------	------	-------------

	0	White
---	---	-------



## Technical Information

All product dimensions are nominal.

Drain location:	Reversible
Basin area, bottom:	61-7/16" x 23-3/4" (1561 mm x 604 mm)
Basin area, top:	47-5/16" x 15-11/16" (1201 mm x 399 mm)
Weight:	48.5 lbs (22 kg)
Minimum floor load:	35.8 lbs/ft <sup>2</sup> (174.8 kg/m <sup>2</sup> )
Water depth:	12-11/16" (322 mm)
Water capacity:	46.21 gal (174.9 L)
Minimum flat for door:	1-7/8" (48 mm)

## Notes

Measure your actual product for rough-in details.

Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.