

Features

- Single-function rainhead
- Full coverage with Katalyst™ air-induction technology offers a drenching spray experience, ideal for rinsing shampoo from hair
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- Optimized sprayface creates a denser uniform spray pattern for consistent coverage and feeling of warmth
- 2.5 gpm (9.5 lpm) maximum flow rate at 45 psi (3.1 bar)
- Metal construction

Material

- KOHLER® finishes resist corrosion and tarnishing

Technology

- Katalyst® air-induction technology infuses water with air, creating bigger drops for a more powerful spray



Installation

- Requires rainhead arm and flange (sold separately)
- G 1/2 inlet connection

**Codes/Standards**

Plumbing Standards
GB/T 23447

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Showerhead/Body Spray:

Rated maximum flow: 2.5 gal/min (9.5 l/min)

Notes

Install this product according to the installation guide.