

Features

- Traditional lever handles allows for both volume and temperature control
- 15 gpm (56.8 l/min) @ 45 psi
- 9-5/8" (244 mm) diverter spout
- Traditional handshower with 60" (1524 mm) hose
- 1/2" (12.7 mm) quarter-turn washerless ceramic disc valves
- Height base: 1-13/16" (46 mm) base to outlet

Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation


- Floor or wall-mount installation

**Codes/Standards**

ASME A112.18.1/CSA B125.1
DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)

KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.



	X
K-126, K-127	27-7/8" (708 mm)
K-128	31-1/2" (800 mm)

Technical Information

All product dimensions are nominal.

Faucet flow rate: 15 gal/min (56.8 l/min)

Handshower rated max flow: 1.75 gal/min (6.6 l/min)

Notes

For use with automatic compensating valves rated at 1.3 gal/min (4.9 l/min) or less.

Install this product according to the installation instructions.