



Ove™
One-piece round-front toilet with skirted trapway,
dual-flush
K-17629T-NS

Features

- One-piece toilets integrate the tank and bowl into a seamless, easy-to-clean design
- Round-front bowl offers an ideal solution for smaller bathrooms and powder rooms
- Rim-to-floor height: 15.35 inches (390 mm)
- Top-mount Polished Chrome dual-flush button offers a choice of 0.8 or 1.6 gpf (3.0 or 6.0 lpf)
- 2.3 inch (58 mm) fully glazed trapway
- Fully skirted trapway simplifies cleaning
- Coordinates with other products in the Ove™ collection
- Compatible with C3™ toilet seats and the Ove™ Quiet-Close toilet seat and lid (sold separately)

Installation

- 7.3 inch (185 mm) P-trap rough-in




Codes/Standards

None Applicable

See website for detailed warranty information.

KOHLER®

Ove™ One-piece round-front toilet with skirted trapway, dual-flush K-17629T-NS



Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Floor
Flush type:	Washdown
Trap passageway:	2" (51 mm)
Rim to water surface:	9-7/8" (251 mm)

Notes

Install this product according to the installation instructions.