

### Features

- Touchless faucet, soap dispenser, and accessory combination designed for Constellation™ 30" wall-mount lavatory systems with backsplash
- Faucet with Kinesis® technology and concealed sensor gives a clean aesthetic and provides extraordinarily accurate and reliable actuation in varying installation environments
- 0.5 gpm (1.9 lpm) maximum flow rate
- On-demand usage with 30-second max. continual run cycle to prevent vandalism and save water
- Vandal-resistant aerator
- Soap dispenser possesses adjustable volume and sensor range for precise actuations
- Soap dispenser requires low (1-20 cps or gr/m-s) viscosity foam soap with no suspended particles. Please see Installation Guide or Maintenance and Use Guide for specific soap recommendations
- Below-counter faucet valving and soap dispenser reservoir reduce footprint and provide easier servicing
- Vandal-resistant sensor on soap dispenser delays dispensing for 30 seconds if blocked for ten seconds
- Above-counter low soap and low battery indicators
- Coordinating bag hook holds purses, backpacks, and other bags
- Includes assembled faucet and soap dispenser, bag hook, multi-outlet power supply, two 10' (3.1 m) cable assemblies, overflow assembly, 1-gallon bulk soap refill, mechanical mixing tee

### Material

- Durable brass construction

### Installation

- Wall-mount



ADA

### Codes/Standards

ASME A112.18.1/CSA B125.1  
NSF/ANSI/CAN 61  
NSF/ANSI/CAN 372  
UL 1310  
ADA  
ICC/ANSI A117.1


### KOHLER® One-Year Limited Warranty


See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

#### Color Code Description

	CP	Polished Chrome
---	----	-----------------



### Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

110/220 V, 50/60 Hz

### Notes

Install this product according to the installation instructions.

ADA compliant when installed to the specific requirements of these regulations.

### Technical Information

All product dimensions are nominal.

Power source: Hardwire - AC and Plug - AC, included

#### Faucet:

Flow rate: 0.5 gal/min (1.9 l/min)

Drain included: Yes

Drain with overflow: No

#### Spout:

Spout reach: 6-3/8" (163 mm)

#### Handshower:

Rated maximum flow: 0 gal/min (0 l/min)

### Pressure/fixture Supply Requirements

Fixture pressure 80 psi (551.6 kPa)

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kohler.com](http://www.kohler.com) USA or [www.kohler.ca](http://www.kohler.ca) Canada

10-22-2024 22:03 - US/CA