

Kumin[®] Curve

Touchless lavatory faucet & soap dispenser with Kinesis® sensor technology, AC-powered, 0.5 gpm K-181029-BK1

Features

- Touchless faucet, soap dispenser, and accessory combination designed for Constellation™ 30" wall-mount lavatory systems
- Faucet with Kinesis[®] technology and concealed sensor gives a clean aesthetic and provides extraordinarily accurate and reliable actuation in varying installation environments
- 0.5 gpm (1.9 lpm) maximum flow rate
- On-demand usage with 30-second max. continual run cycle to prevent vandalism and save water
- Vandal-resistant aerator
- Soap dispenser possesses adjustable volume and sensor range for precise actuations
- Soap dispenser requires low (1-20 cps or gr/m-s) viscosity foam soap with no suspended particles. Please see Installation Guide or Maintenance and Use Guide for specific soap recommendations
- Below-counter faucet valving and soap dispenser reservoir reduce footprint and provide easier servicing
- Vandal-resistant sensor on soap dispenser delays dispensing for 30 seconds if blocked for ten seconds
- Above-counter low soap and low battery indicators
- Coordinating bag hook holds purses, backpacks, and other bags
- Includes assembled faucet and soap dispenser, bag hook, multi-outlet power supply, two 10' (3.1 m) cable assemblies, overflow assembly,1-gallon bulk soap refill, mechanical mixing tee

Material

Durable brass construction

Installation

Deck-mount





Codes/Standards

ASME A112.18.1/CSA B125.1 NSF/ANSI/CAN 61 NSF/ANSI/CAN 372 UL 1310 ADA ICC/ANSI A117.1

KOHLER[®] One-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description




CP Polished Chrome



KOHLER. Faucets

Kumin[®] Curve

Touchless lavatory faucet & soap dispenser with Kinesis® sensor technology, AC-powered, 0.5 gpm K-181029-BK1



Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD). 110/220 V, 50/60 Hz

Technical Information

All product dimensions are nominal.

Power source: Hardwire - AC and Plug - AC, included

Faucet:

Flow rate: 0.5 gal/min (1.9 l/min)

Drain included: Yes

Drain with overflow: No

Spout:

Spout reach: 5-13/16" (148 mm)

Handshower:

Rated maximum 0 gal/min (0 l/min) flow:

Pressure/fixture Supply Requirements

 Fixture pressure
 80 psi (551.6 kPa)

 1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications. For the most current Specification Sheet, go to <u>www.kohler.com</u> USA or <u>www.kohler.ca</u> Canada 10-20-2024 22:37 - US/CA

Notes

Install this product according to the installation instructions.

ADA compliant when installed to the specific requirements of these regulations.

