



**Evok™**  
1700 mm x 750 mm freestanding bath  
**K-18347T**

**Features**

- Freestanding design creates a striking focal point in your bathing area
- 67 inch (1700 mm) x 29.5 inch (750 mm) x 24 inch (610 mm)
- 16.2 inch (411 mm) depth offers a deep soaking experience
- Integral lumbar support

**Material**

- Acrylic

**Installation**


- Freestanding



**Codes/Standards**

None Applicable

See website for detailed warranty information.



## Technical Information

All product dimensions are nominal.

Drain location:	Center
Basin area, bottom:	41-5/16" x 19-3/8" (1050 mm x 492 mm)
Basin area, top:	62-3/8" x 25-1/8" (1585 mm x 639 mm)
Weight:	143.3 lbs (65 kg)
Minimum floor load:	50.8 lbs/ft² (248 kg/m²)
Water depth:	17-1/4" (438 mm)
Water capacity:	63.43 gal (240.1 L)

## Notes

Measure your actual product for rough-in details.

Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

Install this product according to the installation instructions.