

Features

- Unique square 8" (203 mm) single-function rainhead creates a modern look
- 100 nozzles produce a full-coverage rain experience
- Optimized sprayface creates a denser uniform spray pattern for consistent coverage and feeling of warmth
- 2.8 gpm (10.6 lpm) maximum flow rate at 73 psi (5.0 bar)
- Requires shower arm and flange (sold separately)

Material

- Premium material construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Technology

- Katalyst™ air-induction technology infuses water with air, creating bigger drops for a more powerful spray

Installation

- G 1/2 inlet connection
- Ceiling- or wall-mount



Codes/Standards

NOM Standards
NOM 008-CONAGUA


KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	BL	Matte Black
	2MB	Vibrant® Brushed Moderne Brass

**Technical Information**

All product dimensions are nominal.

Shower/Rainhead rated max flow: 2.8 gal/min (10.6 l/min)

Notes

For use with automatic compensating valves rated at 1.6 gal/min (6.1 l/min) or less.

Install this product according to the installation instructions.