



Duo™
1520 mm x 760 mm drop-in bath
K-18776T

Features

- Complements traditional and contemporary bathroom designs
- Rectangular basin creates a spacious bathing experience
- Drop-in design creates a seamless bathroom aesthetic
- 60 inch (1520 mm) x 30 inch (760 mm) x 17 inch (430 mm)
- Round overflow
- 10.83 inch (275 mm) soaking depth provides a relaxing bathing experience
- Integral lumbar support
- Sloping backrest provides comfort

Material

- Acrylic

Installation

- Drop-in

Recommended Products/Accessories

K-17295T Pop-up bath drain, 766 mm cable



Codes/Standards

None Applicable

KOHLER® India Vitreous and bathing Product Limited Warranty


See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	0	White
---	---	-------



Technical Information

All product dimensions are nominal.

Drain location:	Reversible
Basin area, bottom:	40-9/16" x 17-11/16" (1030 mm x 450 mm)
Basin area, top:	56" x 25-11/16" (1422 mm x 653 mm)
Weight:	66.139 lbs (30 kg)
Minimum floor load:	32.9 lbs/ft ² (160.6 kg/m ²)
Water depth:	10-13/16" (275 mm)
Water capacity:	38.383 gal (145.3 L)
Minimum flat for door:	1-1/8" (29 mm)

Notes

Measure your actual product for rough-in details.

Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.