



In-Wall Tank & Carrier System K-18829BR-F

Features

- Robust steel tube frame.
- High density polyethylene tank.
- Insulated tank to prevent sweating.
- Adjustable height allowing the bowl to be set anywhere from 380 mm (15") to 580 mm (23") from the floor.
- Works with dual flush actuator which offers a choice between 3 or 6 liters per flush (.8/1.6 gpf).
- Durable steel frame carrier is installed on studs inside the wall. See installation guide for more detailed information.
- Supply line not included.
- 80 mm (3 3/16") (W) x 1174 mm (46 1/4") (H) x 590 mm (23 1/4") (L)

Required Accessories

K- 8857BR Flush Actuator Plate

or

K- 4177BR Flush Actuator Plate

Recommended Accessories

K-76661BR

K-19045BR

K-4843BR


K-5036BR

K-4952BR

K-6299BR

Components

Additional included component/s: Wall-hung toilet mounting hardware.





Codes/Standards

None Applicable

Kohler® Produtos para Cozinhas e Banheiros Ltda In-Wall Tank Ten-Year Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Water Consumption

Full: 1.6 gpf (6 lpf)

Reduced: 0.8 gpf (3 lpf)

Rough-in: Wall-hung

Fixture Supply Requirements

Max static pressure: 80 psi (551.6 kPa)

Notes

Install this product according to the installation guide.

Refer to manufacturer's instructions and local codes for flush valve requirements.

In-wall tank and carrier system install in wall opening 89 mm (3-1/2") x 590 mm (23-1/4") x 1378 mm (54-1/4") minimum.