



In-Wall Tank K-18829BR-N

Features


- High density polyethylene.
- Insulated tank to prevent sweating.
- Works with dual flush actuator which offers a choice between 3 or 6 liters per flush (.8/1.6 gpf).
- Supply line not included.
- 510 mm (20 1/16") (L) x 530 mm (20 7/8") (H) x 88 mm (3 15/32") (W)

Required Accessories

K- 8857BR Flush Actuator Plate

or

K- 4177BR Flush Actuator Plate





Codes/Standards

None Applicable

Kohler® Produtos para Cozinhas e Banheiros Ltda In-Wall Tank Ten-Year Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Water Consumption

Full: 1.6 gpf (6 lpf)

Reduced: 0.8 gpf (3 lpf)

Rough-in: Wall-hung

Fixture Supply Requirements

Max static pressure: 80 psi (551.6 kPa)

Notes

Install this product according to the installation guide.

Refer to manufacturer's instructions and local codes for flush valve requirements.

In-wall tank and carrier system install in wall opening 89 mm (3-1/2") x 590 mm (23-1/4") x 1378 mm (54-1/4") minimum.