

Features

- One-piece, self-contained ceramic disc valve allows for both volume and temperature control
- 360° swivel spout with 9" (229 mm) clearance
- Quarter-turn washerless ceramic disc valve for filtered water
- Separate lever handle and filtration inlet hose for cold filtered water
- Contemporary European styling
- Flexible supplies
- 2.0 gpm (7.6 lpm) maximum flow rate at 60 psi (4.14 bar)

Material

- Brass

Installation

- Single-hole mounting
- Flexible connections for easy installation

Recommended Products/Accessories

K-23723 Faucet cleaner



ADA

CSA B651

Codes/Standards

ASME A112.18.1/CSA B125.1

NSF/ANSI/CAN 61

NSF/ANSI/CAN 372

All applicable US Federal and State material regulations

DOE - Energy Policy Act 1992

ADA

ICC/ANSI A117.1

CSA B651

IAPMO Certification

KOHLER® Water Filter Systems Five-Year Limited Warranty


See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	CP	Polished Chrome
---	----	-----------------



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 2 gal/min (7.6 l/min)

Drain included: No

Spout:

Spout reach: 7-3/4" (197 mm)

Handshower:

Rated maximum flow: 0 gal/min (0 l/min)

Notes

Install this product according to the installation guide.

This product is not for use with instant hot water systems.

ADA compliant for faucet handles only

ADA, CSA B651 compliant when installed to the specific requirements of these regulations.