



Persuade® Curv

Toilet tank, dual-flush
K-19042-RA

Features

- Right-hand nested trip lever offers a choice of 1.0 or 1.6 gallons per flush (gpf)
- Combines with the K-4326 bowl to create a complete K-75790-RA Persuade Curv toilet
- Dual-flush technology allows you to choose between a full or partial flush

Installation

- Standard 12" (305 mm) rough-in

Recommended Products/Accessories

K-4326 Elongated toilet bowl with skirted trapway
K-23726 Drain treatment



Codes/Standards

ASME A112.19.2/CSA B45.1
ASME A112.19.14
IAPMO Certification

KOHLER® Toilets and Seats Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	0	White
---	---	-------



Persuade® Curv
Toilet tank, dual-flush
K-19042-RA

No image available.
This product is a component and not intended to be a standalone installation.

Technical Information

All product dimensions are nominal.

Toilet type: Bowl-mount
Bowl shape: Elongated
Flush type: Dual-Flush Technology
Rough-in: 12" (305 mm)

Notes

Install this product according to the installation instructions.