



# Persuade® Curv

Toilet tank, dual-flush  
**K-19042**

## Features

- Left-hand nested trip lever offers a choice of 1.0 or 1.6 gallons per flush (gpf)
- Combines with the K-4326 bowl to create a complete K-75790 Persuade Curv toilet
- Dual-flush technology allows you to choose between a full or partial flush

## Installation

- Standard 12" (305 mm) rough-in

## Recommended Products/Accessories

- K-4326 Elongated toilet bowl with skirted trapway
- K-23726 Drain treatment



## Codes/Standards






- ASME A112.19.2/CSA B45.1
- ASME A112.19.14
- IAPMO Certification

## KOHLER® Toilets and Seats Limited Warranty

See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	0	White
	96	Biscuit
	NY	Dune
	95	Ice™ Grey
	7	Black Black™

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kohler.com](http://www.kohler.com) USA or [www.kohler.ca](http://www.kohler.ca) Canada

12-9-2024 21:30 - US/CA

THE BOLD LOOK  
OF **KOHLER**®

No image available.  
This product is a component and not intended to be a standalone installation.

### Technical Information

All product dimensions are nominal.

Toilet type:	Bowl-mount
Waste Outlet:	Floor
Bowl shape:	Elongated
Flush type:	Dual-Flush Technology
Rough-in:	12" (305 mm)

### Notes

Install this product according to the installation instructions.