

Persuade® Curv

Toilet tank, dual-flush K-19042

Features

- Left-hand nested trip lever offers a choice of 1.0 or 1.6 gallons per flush (gpf)
- Combines with the K-4326 bowl to create a complete K-75790 Persuade Curv toilet
- Dual-flush technology allows you to choose between a full or partial flush

Installation

Standard 12" (305 mm) rough-in

Recommended Products/Accessories

K-4326 Elongated toilet bowl with skirted trapway K-23726 Drain treatment



Codes/Standards

ASME A112.19.2/CSA B45.1 ASME A112.19.14 IAPMO Certification

KOHLER® Toilets and Seats Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	0	White
	96	Biscuit
	NY	Dune
	95	Ice™ Grey
	7	Black Black™





Persuade® Curv

Toilet tank, dual-flush K-19042

No image available. This product is a component and not intended to be a standalone installation.

Technical Information

All product dimensions are nominal.

Toilet type: Bowl-mount

Waste Outlet: Floor
Bowl shape: Elongated

Flush type: Dual-Flush Technology

Rough-in: 12" (305 mm)

Notes

Install this product according to the installation instructions.

