



Underscore® | K-1968

48" x 48" drop-in bath

Features

- Spacious design accommodates up to two bathers
- Two raised corner seats
- Extra-deep bathing well for added comfort



Codes/Standards

CSA B45.5/IAPMO Z124

ASTM E162

ASTM E662

Technical Information

All product dimensions are nominal.

Drain Location:	Center
Drain Hole Diameter:	2-1/2" (64 mm)
Basin Area, Bottom:	39-3/8" x 39-3/8" (1000 mm x 1000 mm)
Basin Area, Top:	44-5/8" x 44-5/8" (1133 mm x 1133 mm)
Water Depth:	27-1/2" (699 mm)
Water Capacity:	171 gal (647.3 L)
Minimum Floor Load:	105 lbs/ft ²
Weight:	110 lbs (49.9 kg)
Cutout:	Drop-in, 47" x 47" (1194 mm x 1194 mm)

Material

- Acrylic

Recommended Products/Accessories

K-1177 Tiling-in bead, 144" length

K-23726 Drain treatment

K-23732 Tub & shower cleaner

Warranty

See website for detailed warranty information.

KOHLER® Plastic Baths and Receptors Lifetime Limited
Warranty




1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.

7-29-2026 20:30 - US-CA

No change in measurement if connected with drain illustrated. (K-8150)



Installation

- Center drain
- Undermount
- Drop-in or undermount

Installation Notes

Install this product according to the installation instructions.

Measure your actual product for rough-in details.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

Kit is required for under-mount installations (sold separately).



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.

7-29-2026 20:30 - US-CA