



# Underscore® | K-1969-XHGH

48" x 48" Heated BubbleMassage™ air bath with whirlpool, center drain

## Features

- 122 airjets release thousands of heated bubbles that surround, support, and massage the body
- Variable-speed blower lets you adjust massage intensity to 18 levels
- Eight Proflex® hydromassage jets can be individually adjusted for water flow and direction
- Variable-speed pump for adjusting hydromassage intensity
- Built-in heater
- Automatic and manual purge cycles remove residual water from air channels after use
- 60-minute automatic shutoff timer
- Extra-deep square shape offers fully-immersed soaking experience with a compact footprint
- Spacious design accommodates up to two bathers
- Two integral corner seats
- Integral lumbar support
- Keypad control
- Textured bottom surface



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.  
For the most current specification sheet, go to [www.kohler.com](http://www.kohler.com) USA or [www.kohler.ca](http://www.kohler.ca) Canada.  
7-30-2026 03:08 - US-CA

THE BOLD LOOK  
OF **KOHLER**

## Codes/Standards

ASME A112.19.7/CSA B45.10  
 CSA B45.5/IAPMO Z124  
 ASTM E162  
 ASTM E662  
 UL 1795  
 CSA C22.2 No. 218.2  
 cUL Listed  
 UL Listed

## Technical Information

*All product dimensions are nominal.*

|                        |                                       |
|------------------------|---------------------------------------|
| Drain Location:        | Center                                |
| Drain Hole Diameter:   | 2-3/16" (56 mm)                       |
| Minimum Flat for Door: | 0"                                    |
| Basin Area, Bottom:    | 39-3/8" x 39-3/8" (1000 mm x 1000 mm) |
| Basin Area, Top:       | 44-5/8" x 44-5/8" (1133 mm x 1133 mm) |
| Water Depth:           | 27-1/2" (699 mm)                      |
| Water Capacity:        | 171 gal (647.3 L)                     |
| Minimum Floor Load:    | 102.3 lbs/ft²                         |
| Weight:                | 218 lbs (98.9 kg)                     |

## Material

- Acrylic

## Recommended Products/Accessories

K-1491 Bath/whirlpool pillow, removable  
 K-1601 Bath/whirlpool footstop, removable  
 K-706000-D3 56-5/8"-59-5/8" W x 62" H bypass bath door with 1/4"-thick Frosted glass  
 K-706000-L 56-5/8"-59-5/8" W x 62" H bypass bath door with 1/4"-thick Crystal Clear glass  
 K-706003-L 56-5/8"-59-5/8" W x 62" H sliding bath door with 3/8"-thick Crystal Clear glass  
 K-706004-D3 56-5/8"-59-5/8" W x 62" H bypass bath door with 1/4"-thick Frosted glass  
 K-706004-L 56-5/8"-59-5/8" W x 62" H bypass bath door with 1/4"-thick Crystal Clear glass  
 K-706007-L 56-5/8"-59-5/8" W x 62" H sliding bath door with 3/8"-thick Crystal Clear glass

## Required Products/Accessories

- K-9698 Whirlpool trim kit with eight jets
  - K-7271 Slotted overflow brass bath drain
- or
- K-9698 Whirlpool trim kit with eight jets
  - K-7272 Slotted overflow bath drain

## Technology

- Heated BubbleMassage™ technology warms and humidifies air before it enters the bath



## Required Electrical Service

Three dedicated circuits required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

|                 |                    |
|-----------------|--------------------|
| Blower:         | 120 V, 15 A, 60 Hz |
| Air bath, Pump: | 120 V, 15 A, 60 Hz |
| Heater:         | 120 V, 15 A, 60 Hz |

## Electrical Component Ratings


|           |                    |
|-----------|--------------------|
| Blower:   | 120 V, 10 A        |
| Air bath: | 120 V, 5 A, 60 Hz  |
| Pump:     | 120 V, 7 A, 60 Hz  |
| Heater:   | 120 V, 12 A, 60 Hz |

## Warranty

*See website for detailed warranty information.*

KOHLER® Plastic Baths and Shower Bases Lifetime Limited Warranty|KOHLER® Hydrotherapy Components Five-Year Limited Warranty





## Installation

- Drop-in or undermount
- Center drain
- 120 V electrical requirement allows for easy installation with standard outlet
- Requires three dedicated circuits

## Installation Notes

*Install this product according to the installation instructions.*

Measure your actual product for rough-in details.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

