

### Features

- Low-threshold design for easy entry and exit
- Single threshold for three-wall installation
- Integral 18" (457 mm) undercut seat at left
- Coordinates with other products in the Tresham collection

### Material

- Acrylic

### Installation

- Right drain

### Recommended Products/Accessories

- K-706009-D3 Frameless Sliding Shower Door
- K-706009-L Frameless Sliding Shower Door
- K-706015-D3 Frameless Sliding Shower Door
- K-706015-L 74" H sliding shower door with 1/4"-thick glass
- K-9132 Shower Drain
- K-23726 Drain treatment
- K-23732 Tub & shower cleaner



### Codes/Standards





- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662
- IAPMO Certification


### KOHLER® Plastic Baths and Receptors Lifetime Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	0	White
	96	Biscuit
	NY	Dune
	95	Ice™ Grey



## Technical Information

All product dimensions are nominal.

Drain location:	Right
Weight:	79.5 lbs (36.1 kg)
Minimum floor load:	20 lbs/ft <sup>2</sup> (97.6 kg/m <sup>2</sup> )
Minimum flat for door:	2-1/2" (64 mm)

## Notes

Measure your actual product for rough-in details.

Install this product according to the installation instructions.

Shimming may be required between the stud frame and the fixture.

Stud opening tolerance is +1/4" (6 mm), -0" (0 mm).

KOHLER steam generator/control kit are designed for use with this product. Kohler Co. shall not be responsible for problems encountered due to the installation and use of other manufacturer's steam generators.