

Features

- Single Lever handle provides on/off activation and volume control for both outlets
- For use with cold water line only
- 130 mm (5.1 inch) spout reach
- 6.0 gpm (22.7 lpm) maximum flow rate at 45 psi (3.1 bar)
- Coordinates with other products in the Aleo® collection

Material

- Brass construction ensures durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- Wall-mount
- G 1/2 (13 mm) inlet connection



Codes/Standards

None Applicable

KOHLER® India Faucet, Sanitaryware and Bathing Products Limited Warranty

See website for detailed warranty information.


Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------



CP	Polished Chrome
----	-----------------



Technical Information

All product dimensions are nominal.

Faucet flow rate: 6 gal/min (22.7 l/min)

Notes

Install this product according to the installation instructions.