

## Features

- 3.14 inch (80 mm) tank width offers condensed installation space
- Minimal noise as water fills in
- Large flush actuator opening; remove faceplate for easy access to inner tank
- Mechanical flush valve for standard push-button actuation
- Dual-flush technology offers a choice of 0.8 or 1.6 gpf (3.0 or 6.0 lpf)
- Blow molding ensures sturdy single body construction to prevent leaks
- Independent filter offers easy access for cleaning
- In-wall tank, frame, and dual-flush actuator only; requires wall-hung bowl, dual-flush faceplate, and seat (sold separately)

## Material

- Premium material construction for durability and reliability

## Installation

- Durable steel frame carrier is installed on solid wall. See installation guide for more detailed information
- Supply line sold separately



## Codes/Standards

None Applicable

## KOHLER® India Faucet, Sanitaryware and Bathing Products Limited Warranty


See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

## Color Code Description

NP



## Technical Information

All product dimensions are nominal.

Toilet type: In-wall mount

Flush type: Mechanical

Rough-in: 10" (254 mm)

## Notes

Install this product according to the installation instructions.