

Features

- ContinuousClean system automatically dispenses cleaning solution with every flush
- Works with any white toilet bowl cleaner tablet. Tablets last for more than one year in ContinuousClean system
- Revolution 360® flushing technology generates a forceful swirling motion to keep the bowl clean longer
- 1.28 gpf (4.8 lpf)
- Left-hand Polished Chrome trip lever
- Combines with the K-20148 bowl to create a complete K-20198 Betello™ ContinuousClean toilet
- Adjustment dial lets you set how much cleaning solution is dispensed with every flush
- Optional: uses two AAA batteries (included) to power the LED system indicator light
- AquaPiston® canister optimizes the flow out of the tank, harnessing gravity and the natural powerful reducing cascade of water to increase the power and effectiveness of the flush

Installation

- Supply line sold separately

Recommended Products/Accessories

K-20148 Elongated toilet bowl with skirted trapway
K-23726 Drain treatment



Codes/Standards






ASME A112.19.2/CSA B45.1

KOHLER® Toilets and Seats Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	0	White
	96	Biscuit
	NY	Dune
	95	Ice™ Grey
	7	Black Black™

No image available.
This product is a component and not intended to be a standalone installation.

Technical Information

All product dimensions are nominal.

Toilet type: Bowl-mount
Waste Outlet: Floor
Flush type: Revolution 360, AquaPiston

Fixture Supply Requirements

Min static pressure: 15 psi (103.4 kPa)
Max static pressure: 80 psi (551.6 kPa)

Notes

Install this product according to the installation instructions.