



Irvine® | K-20205-RA

Toilet tank, 1.28 gpf

Features

- 1.28 gpf (4.8 lpf)
- Right-hand Polished Chrome trip lever
- Combines with the K-20485 bowl to create a complete K-20450-RA Irvine™ toilet
- AquaPiston® canister optimizes the flow out of the tank, harnessing gravity and the natural, powerful reducing cascade of water to increase the power and effectiveness of the flush
- Easy-to-flush canister design requires less force to actuate than a 3" (76 mm) flapper, and has 90% less exposed seal material which resists conditions that cause wear, tear, shrinkage and swelling



Sustainability



Available Colors/Finishes

Color tiles intended for reference only.

0 White



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
8-22-2026 13:00 - US-CA

THE BOLD LOOK
OF **KOHLER**

Codes/Standards

Plumbing codes may require elongated toilets and elongated, open-front seats in public bathrooms.



ASME A112.19.2/CSA B45.1

EPA WaterSense®

Technical Information

Flush Type: AquaPiston

Flush Rate: 1.28 gpf (4.8 lpf)

Recommended Products/Accessories

K-23726 Drain treatment

K-21265-R Right-hand trip lever

K-20485 Elongated toilet bowl with skirted trapway

Warranty

See website for detailed warranty information.

KOHLER® Toilets and Seats Limited Warranty



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.

8-22-2026 13:00 - US-CA

No image available.

This product is a component and not intended to be a standalone installation.

Installation

- Supply line sold separately
-

Installation Notes

Install this product according to the installation instructions.

Product dimensions are nominal and may vary per ASME
A112.19.2 tolerances.

