

Features

- 8" (203 mm) widespread faucet holes
- Oval basin
- Overflow drain
- Combination consists of the K-2028-8 sink and the K-2057 shroud

Material

- Vitreous china

Installation

- Wall-mount

Recommended Products/Accessories

- K-7605-P Angle Supply with Stop (pair)
- K-8998 P-Trap
- K-23726 Drain treatment
- K-23725 Cast iron cleaner

Included Components

- K-2028-8 22" oval wall-mount bathroom sink
- K-2057 Bathroom Sink Shroud



ADA

OBC

Codes/Standards

ASME A112.19.2/CSA B45.1
ADA
ICC/ANSI A117.1
OBC
IAPMO Certification

KOHLER® Vitreous China Bathroom Sink Lifetime Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes


Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------



0

White



Technical Information

All product dimensions are nominal.

Basin configuration:	Single Bowl
Center(s):	8" (203 mm)
Bowl area (Only):	Length: 18" (457 mm) Width: 12" (305 mm) Water depth: 4" (102 mm)
With overflow:	Yes
Number of deck holes:	3
Faucet hole(s):	1-3/8" (35 mm)
Drain hole:	1-3/4" (44 mm)

Notes

Install this product according to the installation instructions.

ADA, OBC compliant when installed to the specific requirements of these regulations.