



Tend™

Wall-mount urinal with rear spud, 0.5 – 3.8 lpf
K-20713IN-ER

Features

- Compact, modern wash-down urinal with no exposed bolt connections
- 0.125 - 1.0 gpf (0.47 - 3.8 lpf)
- Delivers dependable water-saving performance and added hygiene
- Smooth contours make cleaning fixture fast and easy
- Extended lip helps keep floor cleaner
- Optimized interior design virtually eliminates splashing
- G 1/2 (13 mm) rear spud
- Fully skirted trapway simplifies cleaning
- Rigid snap-in stainless steel strainer increases drain flow speed and eliminates shifting
- Requires wall-mount faceplate (sold separately)

Installation

- Trapway secures urinal to wall, eliminating bolts for a faster installation
- Wall-mount



Codes/Standards



None Applicable


KOHLER® Bath and Shower Doors Commercial One-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	0	White
	7	Black Black™



Technical Information

All product dimensions are nominal.

Flush Type:	Washdown
Spud size:	1/2, Inlet, Rear
Min. Water per Flush:	0.125 gpf (0.5 lpf)
Max. Water per Flush:	1 gpf (3.8 lpf)

Designed for the above water use when installed with a water-saving flushometer.

Pressure and Supply Requirements

Fixture pressure min (static):	25 psi (172.4 kPa)
Fixture flow rate min:	3 gpm (11.4 lpm)
Fixture pressure max (static):	80 psi (551.6 kPa)

Notes

Install this product according to the installation instructions.