

### Features

- One knob handle for volume/temperature and one to adjust water outlet/flow
- Red/blue indexing
- Temperature memory allows faucet to be turned on and off at the temperature set during prior usage

### Material

- Premium metal construction
- KOHLER® finishes resist corrosion and tarnishing

### Technology

- Thermostatic technology automatically maintains temperature within +/- 0.4°C (+/- 0.72°F) during water pressure fluctuations

### Installation

- Semi-recessed into wall

### Adapters, Rough-in and Extension Kits

1226034.asm



Range: 2-11/16" (69 mm) -  
2-11/16" (69 mm)



### Codes/Standards

Plumbing Standards  
QB/T 2806

See website for detailed warranty  
information.



**Technical Information**

All product dimensions are nominal.

Drain included: No

**Notes**

Install this product according to the installation instructions.