

### Features

- Wide coverage spray produces an encompassing spray for everyday use
- Showerhead rotates 360° for customized user height within 4¾" (121 mm)
- 1.5 gpm (5.7 lpm) maximum flow rate showerhead allows you to save water without sacrificing performance or coverage
- Variable-flow lever lets you adjust from 1.5 gpm (5.7 lpm) down to 0.5 gpm (1.9 lpm) water pause for greater conservation during your shower routine
- Sprayface resists hard water buildup and is easy to clean
- Silicone sprayface is easy to clean
- This product can help a building earn Water Efficiency points in LEED® Green Building Rating System

### Material

- KOHLER® finishes resist corrosion and tarnishing

### Technology

- Katalyst® air-induction technology infuses water with air, creating bigger drops for a more powerful spray

### Installation

- Shower arm and flange (sold separately) required for wall-mount installation

### Recommended Products/Accessories

K-23723 Faucet cleaner






### Codes/Standards



ASME A112.18.1/CSA B125.1  
DOE - Energy Policy Act 1992  
EPA WaterSense®  
California Energy Commission (CEC)  
IAPMO Certification

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

| Color   | Code | Description             |
|---|------|-------------------------|
|  | CP   | Polished Chrome         |
|  | BN   | Vibrant® Brushed Nickel |
|  | BL   | Matte Black             |



### Technical Information

All product dimensions are nominal.

#### Showerhead/Body Spray:

Rated maximum flow: 1.5 gal/min (5.7 l/min)