

Features

- Handshower features contemporary design
- Ergonomic design is comfortable and easy to grip
- Advanced spray engine provides two spray experiences: full coverage and targeted massage
- Simple thumb button allows for a smooth transition between sprays
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- 2.5 gpm (9.5 lpm) maximum handshower flow rate at 80 psi (5.5 bar)
- Requires shower hose (sold separately)

Material

- Premium material construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing


Installation

- Bracket or sidebar required for wall-mount installation (sold separately)
- Deck-mount holder required for deck-mount installation (sold separately)

**Codes/Standards**

None Applicable

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Handshower rated max flow: 2.5 gal/min (9.5 l/min)

Pressure/fixture Supply Requirements

Fixture pressure 72 psi (496.4 kPa)
max (static):

Fixture pressure min 8 psi (55.2 kPa)
(static):

Notes

Install this product according to the installation instructions.