



Conical Bell™

413 mm round vessel bathroom sink with glazed underside, no overflow

K-2200IN

Features

- Traditional design creates a classic look
- Round basin
- No faucet holes; requires wall- or tall deck-mount faucet
- Center drain, no overflow
- Glazed underside offers beauty from all angles

Material

- Vitreous china

Installation

- Semi-recessed vessel
- Drops partially below vanity top; requires countertop cutout

Required Products/Accessories

K-20746IN Bathroom sink grid drain without overflow
K-75823IN 32 mm x 32 mm bottle trap

Recommended Products/Accessories

K-24740IN Ceramic cap drain without overflow



Codes/Standards





None Applicable

KOHLER® India Faucet, Sanitaryware and Bathing Products Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes



Color tiles intended for reference only.

Color	Code	Description
	0	White
	K4	Cashmere
	7	Black Black™
	DGS	Indigo Gloss



Conical Bell™

413 mm round vessel bathroom sink with glazed underside, no overflow
K-2200IN



Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl

Min. base cabinet width: 18-1/4" (464 mm)

Bowl area (Basin #1): Bowl depth: 4-3/8" (111 mm)

With overflow: No

Drain hole: 1-3/4" (44 mm)

Notes

Install this product according to the installation instructions.