KOHLER, Faucets

Simplice®

Single-handle bar sink faucet K-22034

Features

- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- High-arch swing spout with 180° rotation offers superior clearance for filling pitchers, chilling bottles and cleanup
- Temperature memory allows faucet to be turned on and off at the temperature set during prior usage
- 1.5 gpm (5.7 lpm) maximum flow rate at 60 psi (4.14 bar)

Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Single-hole installation
- Flexible supply lines simplify installation

Recommended Products/Accessories

1054432 1.5 GPM (5.7 l/min) Aerator Kit K-77685 Single-cartridge water filtration system

K-77686 Double-cartridge water filtration system

K-77687 single replacement filter cartridge

K-77688 Replacement Filter Cartridges, Two-Pack

K-23723 Faucet cleaner



ADA C

CSA B651

Codes/Standards

ASME A112.18.1/CSA B125.1 NSF/ANSI/CAN 61

NSF/ANSI/CAN 372

All applicable US Federal and State material regulations

DOE - Energy Policy Act 1992

California Energy Commission (CEC)

ADA

ICC/ANSI A117.1

CSA B651

IAPMO Certification

KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.


Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	VS	Vibrant® Stainless
	BL	Matte Black
	2MB	Vibrant® Brushed Moderne
		Brass



Simplice® Single-handle bar sink faucet K-22034



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 1.5 gal/min (5.7 l/min)

Drain included: No

Spout:

Spout reach: 7-1/4" (185 mm)

Handshower:

Rated maximum 0 gal/min (0 l/min)

flow:

Notes

Install this product according to the installation instructions.

ADA compliant for faucet handles only ADA, CSA B651 compliant when installed to the specific requirements of these regulations.

