



Caxton™
54 cm undercounter lavatory
K-2211IN

Features

- Transitional design combines the best of modern and classic styles
- Oval basin
- No faucet holes; requires wall- or deck-mount faucet
- Rear drain and overflow

Material

- Vitreous china

Installation

- Undermount

Recommended Products/Accessories

K-45432IN Bathroom sink grid drain with overflow
K-75823IN 32 mm x 32 mm bottle trap

Included Components

1193643 Basin clamps



Codes/Standards

None Applicable


**KOHLER® India Faucet,
Sanitaryware and Bathing
Products Limited Warranty**


See website for detailed warranty
information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	0	White
---	---	-------



Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl

Min. base cabinet width: 21-3/16" (538 mm)

Bowl area (Basin #1):
Length: 15" (380 mm)
Width: 18-7/8" (480 mm)
Water depth: 5-1/4" (133 mm)

With overflow: Yes

Drain hole: 1-3/4" (44 mm)

Template: 117215-IN01, required, included

Notes

Install this product according to the installation instructions.