



Ladena™
591 mm rectangular undercounter bathroom sink
K-2215M

Features

- Rectangular basin with curved bottom
- With overflow
- No faucet holes; requires wall- or counter-mount faucet

Material

- Vitreous china

Installation

- Undermount
- Hardware kit included

Recommended Products/Accessories

K-8998 P-Trap
K-23726 Drain treatment
K-23725 Cast iron cleaner

Included Components

1193643 Basin clamps



Codes/Standards

None Applicable

KOHLER® Vitreous China Bathroom Sink Lifetime Limited Warranty


See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description

	7	Black Black™
---	---	--------------



Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl

Min. base cabinet width: 24" (610 mm)

Bowl area: Length: 20-5/8" (524 mm)
Width: 13-5/8" (346 mm)
Water depth: 4-5/8" (117 mm)

With overflow: Yes

Drain hole: 1-3/4" (44 mm)

Template: Undermount, 1245229-7, required, included

Notes

Install this product according to the installation instructions.