



Vintage®
Under-mount Bathroom Sink
K-2240

Features

- Classic oval basin.
- Overflow drain.

Material

- Vitreous china.

Installation

- No faucet holes; requires wall-or counter-mount faucet.
- Undermount.

Recommended Products/Accessories

K-8998 P-Trap
K-23726 Drain treatment
K-23725 Cast iron cleaner

Included Components

Additional Components:

1193643 Basin clamps
Adjustable linkage



ADA

CSA B651

Codes/Standards

ASME A112.19.2/CSA B45.1
ADA
ICC/ANSI A117.1
CSA B651

KOHLER® One-Year Limited Warranty

See website for detailed warranty information.



Available Colors/Finishes

Color tiles intended for reference only.


Color	Code	Description
	0	White
	HW1	Honed White
	96	Biscuit
	47	Almond
	58	Thunder™ Grey
	7	Black Black™

KOHLER®

Vintage® Under-mount Bathroom Sink K-2240



Note: Waterproof unprotected overhang area on the underside of wood counter.



Notes

Install this product according to the installation instructions.

NOTICE: Countertop manufacturer or cutter must use the current product template available at www.kohler.com, or by calling 1-800-4KOHLER. Kohler Co. is not responsible for cutout errors when the incorrect cutout template is used.

ADA, CSA B651 compliant when installed to the specific requirements of these regulations.

Technical Information

All product dimensions are nominal.

Bowl configuration: Single

Installation: Under-mount

Bowl area (Only): Length: 21" (533 mm)
Width: 12" (305 mm)
Water depth: 4-7/8" (124 mm)

Drain hole: 1-3/4" (44 mm)

Template: 1046699-7, required, not included