



Simpalo® | K-22519-CHLED

28" LED chandelier

Features

- A great piece for almost any space — especially in a foyer or dining room
- Dimmable, integrated LED emits beautiful ambient light at the perfect color temperature
- Downrods offer additional height options
- Suitable for damp locations, per UL 1598



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
7-30-2026 01:59 - US-CA

THE BOLD LOOK
OF **KOHLER**

Codes/Standards

CSA C22.2 No. 250.0
CA Title 24 JA8
cETL Listed
ETL Listed

Technical Information

All product dimensions are nominal.

Number of Lights:	2
Lighting Type:	Integrated LED
Number of Shades:	1
Hanging Type:	Downrod
Downrod Detail:	3 x 12" (305 mm)
Height:	22-1/4" (565 mm) - 46-1/4" (1174 mm)

Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes

Required Electrical Service

One dedicated circuit required.

Lights: 120 V, 0.977 A, 60 Hz

Electrical Component Ratings


LED: 60 Hz, 40 W, 6000 Lumens

Warranty

See website for detailed warranty information.

KOHLER® Indoor Lighting Fixtures Limited Warranty





Installation Notes

Install this product according to the installation instructions.



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.

7-30-2026 01:59 - US-CA