

## Features

- Single handle provides on/off activation, volume, and temperature control
- Red/blue indexing on handle
- 3.94 inch (100 mm) spout height
- 4.75 inch (120 mm) spout reach
- 3.69 gpm (14.0 lpm) maximum flow rate at 43.5 psi (3.0 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Includes installation hardware
- Coordinates with other products in the Hone™ collection to complete your bathroom

## Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

## Installation

- Deck-mount
- Single-hole installation



## Codes/Standards




None Applicable


## KOHLER® India Faucet Limited Warranty

See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CP	Polished Chrome
	AF	Vibrant® French Gold
	BN	Vibrant® Brushed Nickel



## Technical Information

All product dimensions are nominal.

Drain included: No

Drain with overflow: No

## Notes

Install this product according to the installation guide.