

Features

- Sleek, minimalist design
- Single handle provides on/off activation, volume, and temperature control
- Red/blue indexing on handle
- 6.6 inch (167 mm) spout reach
- 2.2 gpm (8.3 lpm) maximum flow rate at 43.5 psi (3.0 bar)
- Laminar flow
- Valve sold separately
- Drain sold separately
- Coordinates with other products in the Hone® collection to complete your bathroom

Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- Wall-mount



Codes/Standards

None Applicable


KOHLER® India Faucet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	AF	Vibrant® French Gold



Technical Information

All product dimensions are nominal.

Faucet flow rate: 2.2 gal/min (8.3 l/min)

Spout:

Spout reach: 6-1/2" (166 mm)

Notes

Install this product according to the installation guide.