

KOHLER® Faucets

Wall-mount single-handle bathroom sink faucet, 7.5 lpm
Hone®
K-22540IN-4ND

Features

- Single handle provides on/off activation, volume, and temperature control
- Red/blue indexing on handle
- 6.5 inch (165 mm) spout reach
- 2.0 gpm (7.5 lpm) maximum flow rate at 43.5 psi (3.0 bar)
- Coordinates with other products in the Hone™ collection to complete your bathroom
- Drain sold separately

Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- Wall-mount
- Trim only; requires valve to complete installation (sold separately)

Required Products/Accessories

K-5679IN Single-handle wall-mount bathroom sink faucet valve



Codes/Standards




None Applicable



KOHLER® India Faucet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	AF	Vibrant® French Gold
	BN	Vibrant® Brushed Nickel



Technical Information

All product dimensions are nominal.

Drain included: No

Notes

Install this product according to the installation guide.