



Damask®
One-light lacemaker sconce
K-22546-SC01

Features

- Derived from historical references this lighting collection is intricate and modern at the same time
- Suitable for living, dining, and kitchen spaces, allowing you to create a cohesive design aesthetic throughout your home
- Candelabra base (E12) socket, works best with type G or T light bulbs (sold separately)
- Includes installation hardware
- Suitable for damp locations, per UL 1598

Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes

Recommended Products/Accessories

K-23723 Faucet cleaner





Codes/Standards

UL 1598
CSA C22.2 No. 250.0
cETL Listed
ETL Listed

**KOHLER® Indoor Lighting Fixtures
Limited Warranty**

See website for detailed warranty information.



Required Electrical Service

One circuit required.

Lights: 120 V, 0.5 A, 60 Hz

Technical Information

All product dimensions are nominal.

Material: Brass
Number of Lights: 1
Lighting Type: Socket-based
Socket Type: E-12 Candelabra
Number of Shades: 1
Shade Type: Glass - clear
Hanging Type: Non-hanging
Downrod Detail: 0 x
Electrical component rating: Socket Rating: 60 Hz, 60 W, 450 Lumens, 2300K