

### Features

- Versatile, contemporary design
- Two Lever handles offer separate control of hot and cold water
- Red/blue indexing on handles
- 8-5/8" (219 mm) spout reach
- Aerated flow
- Stationary spout
- 2.2 gpm (8.3 lpm) maximum flow rate at 45 psi (3.1 bar)
- Includes metal pop-up drain with 1-1/4" (32 mm) tailpiece
- Coordinates with other products in the Parallel collection
- Requires valve (sold separately)

### Material

- Premium material construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

### Installation


- Wall-mount
- Requires wall-mount K-31141T valve (sold separately)



### Codes/Standards

Plumbing Standards  
GB 18145

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

#### Faucet:

Flow rate: 2.2 gal/min (8.3 l/min)

Drain included: Yes

Drain with overflow: No

#### Spout:

Spout reach: 8-5/8" (219 mm)

### Notes

Install this product according to the installation instructions.