

Features

- Complements Artifacts faucets and accessories
- Versatile design that features a frosted shade surrounded by a clear glass shade
- For a vintage look, remove the optional frosted glass and add any E26 medium-base Edison bulb (sold separately)
- For soft lighting, use an E26 medium-base type B light bulb with the frosted shade (bulb sold separately)
- A 7.5' (2.3 m) cord offers many height options
- Fixture is dimmable when paired with dimmer switch and compatible bulbs

Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes

Recommended Products/Accessories

K-23723 Faucet cleaner



Codes/Standards


UL 1598
CSA C22.2 No. 250.0
cETL Listed
ETL Listed


KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	SNL	Polished Nickel
	CPL	Polished Chrome



Required Electrical Service

One circuit required.

Lights: 120 V, 0.333 A, 60 Hz

Technical Information

All product dimensions are nominal.

Material: Brass

Number of Lights: 1

Lighting Type: Socket-based

Socket Type: E-26 Medium

Number of Shades: 2

Shade Type: Frosted Glass

Hanging Type: Adjustable pulley

Height: $18\text{-}1/2''$ (470 mm) - $138\text{-}1/2''$ (3518 mm)

Electrical component rating: Socket Rating: 60 Hz, 40 W, 450 Lumens, 3000K