

## Features

- Complements Artifacts faucets and accessories
- Versatile design that features a frosted shade surrounded by a clear glass shade
- For a vintage look, remove the optional frosted glass and add any E26 medium-base Edison bulb (sold separately)
- For soft lighting, use an E26 medium-base type B light bulb with the frosted shade (bulb sold separately)
- A 7.5' (2.3 m) cord offers many height options
- Fixture is dimmable when paired with dimmer switch and compatible bulbs

## Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes

## Recommended Products/Accessories

K-23723 Faucet cleaner



## Codes/Standards



UL 1598  
CSA C22.2 No. 250.0  
cETL Listed  
ETL Listed


## KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	SNL	Polished Nickel
	CPL	Polished Chrome



## Required Electrical Service

One circuit required.

Lights: 120 V, 1 A, 60 Hz

## Technical Information

All product dimensions are nominal.

Material: Brass  
Number of Lights: 3  
Lighting Type: Socket-based  
Socket Type: E-26 Medium  
Number of Shades: 3  
Shade Type: Frosted Glass  
Hanging Type: Cord  
Height: 26-3/8" (671 mm) - 146-3/8" (3719 mm)  
Electrical component rating: Socket Rating: 60 Hz, 40 W, 800 Lumens, 3000K