

Features

- Complements Artifacts faucets and accessories
- Versatile design that features three frosted shades surrounded by one large clear glass shade
- For a vintage look, remove the optional frosted glass and add any E26 medium-base Edison bulb (sold separately)
- For soft lighting, use an E26 medium-base type B light bulb with the frosted shade (bulb sold separately)
- 6 accent chain offers additional height options
- Fixture is dimmable when paired with dimmer switch and compatible bulbs

Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes

Recommended Products/Accessories

K-23723 Faucet cleaner




Codes/Standards

UL 1598
CSA C22.2 No. 250.0
cETL Listed
ETL Listed

KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.



Required Electrical Service

One circuit required.

Lights: 120 V, 1 A, 60 Hz

Technical Information

All product dimensions are nominal.

Material: Brass
 Number of Lights: 3
 Lighting Type: Socket-based
 Socket Type: E-26 Medium
 Number of Shades: 4
 Shade Type: Glass - clear, Glass - frosted
 Hanging Type: Chain
 Downrod Detail: 1 x 17-5/16" (439 mm)
 Height: 38-9/16" (979 mm) -
 108-5/8" (2759 mm)
 Electrical component rating: Socket Rating: 60 Hz, 40 W, 1200
 Lumens, 3000K