

## Features

- Complements Artifacts faucets and accessories
- Versatile design that features a frosted shade surrounded by a clear glass shade
- For a vintage look, remove the optional frosted glass and add any E26 medium-base Edison bulb (sold separately)
- For soft lighting, use an E26 medium-base type B light bulb with the frosted shade (bulb sold separately)
- Three 10' (3.1 m) cords offer many height options
- Includes installation hardware
- Fixture is dimmable when paired with dimmer switch and compatible bulbs

## Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes

## Recommended Products/Accessories

K-23723 Faucet cleaner



## Codes/Standards



UL 1598  
CSA C22.2 No. 250.0  
cETL Listed  
ETL Listed


## KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	SNL	Polished Nickel
	CPL	Polished Chrome



## Required Electrical Service

One circuit required.

Lights: 120 V, 1 A, 60 Hz

## Technical Information

All product dimensions are nominal.

Material: Brass

Number of Lights: 3

Lighting Type: Socket-based

Socket Type: E-26 Medium

Number of Shades: 6

Shade Type: Glass - frosted, Glass - clear

Hanging Type: Cord

Height: 14-5/16" (363 mm) -  
134-5/16" (3411 mm)

Electrical component rating: Socket Rating: 60 Hz, 40 W, 1200  
Lumens, 3000K