



Artifacts®
27-1/2" adjustable linear chandelier
K-22659-CH03

Features

- Complements Artifacts faucets and accessories
- Versatile design that features a frosted shade surrounded by a clear glass shade
- For a vintage look, remove the optional frosted glass and add any E26 medium-base Edison bulb (sold separately)
- For soft lighting, use an E26 medium-base type B light bulb with the frosted shade (bulb sold separately)
- Three 10' (3.1 m) cords offer many height options
- Includes installation hardware
- Fixture is dimmable when paired with dimmer switch and compatible bulbs

Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes

Recommended Products/Accessories

K-23723 Faucet cleaner




Codes/Standards

UL 1598
CSA C22.2 No. 250.0
cETL Listed
ETL Listed

**KOHLER® Indoor Lighting Fixtures
Limited Warranty**

See website for detailed warranty information.



Required Electrical Service

One circuit required.

Lights: 120 V, 1 A, 60 Hz

Technical Information

All product dimensions are nominal.

Material: Brass
Number of Lights: 3
Lighting Type: Socket-based
Socket Type: E-26 Medium
Number of Shades: 6
Shade Type: Glass - frosted, Glass - clear
Hanging Type: Adjustable pulley
Height: 18-1/2" (470 mm) - 138-1/2" (3518 mm)
Electrical component rating: Socket Rating: 60 Hz, 40 W, 1200 Lumens, 3000K