

Features

- Complements Artifacts faucets and accessories
- Versatile design that features a frosted shade surrounded by a clear glass shade
- For a vintage look, remove the optional frosted glass and add any E26 medium-base Edison bulb (sold separately)
- For soft lighting, use an E26 medium-base type B light bulb with the frosted shade (bulb sold separately)
- Two 6", two 12", and four 18" downrods offer many height options
- Includes installation hardware
- Fixture is dimmable when paired with dimmer switch and compatible bulbs

Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes




Codes/Standards

UL 1598
CSA C22.2 No. 250.0
cETL Listed
ETL Listed

KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.



Required Electrical Service

One circuit required.

Lights: 120 V, 1.666 A, 60 Hz

Technical Information

All product dimensions are nominal.

Material: Brass

Number of Lights: 5

Lighting Type: Socket-based

Socket Type: E-26 Medium

Number of Shades: 10

Shade Type: Glass - frosted, Glass - clear

Hanging Type: Downrod

Downrod Detail: 1 x 12" (305 mm), 1 x 6" (152 mm), 4 x 18" (457 mm)

Height: 23-11/16" (602 mm) - 71-11/16" (1821 mm)

Electrical component rating: Socket Rating: 60 Hz, 40 W, 2000 Lumens, 3000K